


Dione 1280 CAM Series



STATE-OF-THE-ART THERMAL IMAGING CORE

KEY FEATURES



**STATE-OF-THE-ART MICROBOLOMETER
DETECTOR WITH 12 μm PIXEL PITCH**



FRAME RATES UP TO 60 Hz



**INDUSTRY LEADING LOW SWaP
(SIZE, WEIGHT AND POWER)**

The Dione 1280 CAM series is based on an uncooled microbolometer detector with a 1280x1024 pixel resolution and 12 μm pitch. The detector NETD is less than 40 mK (available upon request) or 50 mK. Dione 1280 CAM is a LWIR uncooled thermal imaging core with housing supporting M34/M45 lens (optional).

All Dione 1280 versions benefit from Xenics image enhancement for advanced image processing while keeping power consumption low. Moreover, GenICam compliance and availability of multiple lenses add flexibility for integration programs in the target markets like defense and surveillance, transportation and industrial process monitoring.

Camera Specifications	Dione 1280 CAM 40 mK	Dione 1280 CAM 50 mK
Mechanical specifications		
Approx. camera dimensions (width x height x length) [mm]	40 x 40 x 35 (M34 - 16bit DV); 50 x 50 x 36 (M45 - 16bit DV); 40x40x40 (M34 - MIPI CSI-2, USB), 50x50x41 (M45 - MIPI CSI-2, USB)	
Optical interface (optional)	M34x0.5 or M45x 0.75	
Camera weight [gr]	78 (M34 - 16bit DV); 80 (M45 - 16bit DV); 88 (M34 - USB); 90 (M45 - USB); 89 (M34 - MIPI CSI-2); 91 (M45 - MIPI CSI-2)	
Connector general I/O	SAMTEC ST5-30-1.50-L-D-P-TR [16bit DV]; 22-pin FFC/FPC connector (Molex) [MIPI CSI-2]; Type B USB 3.0 [USB]	
Environmental & power specifications		
Operating temperature range (housing temperature) [°C]	From -40 to +70 (16bit DV, USB); From -30 to +70 (MIPI CSI-2)	
Storage temperature [°C]	From -40 to +85 (16bit DV, USB); From -30 to +85 (MIPI CSI-2)	
Power consumption [W]	1.9 (at 30 Hz operation - 16bit DV) and 2.1 (at 60 Hz operation - 16bit DV); < 2.7 (MIPI CSI-2, USB)	
Power supply voltage	DC 5 V	
Shock	40 g, 11 ms, according to MIL-STD810G	
Vibration	5 g (20 to 2000 Hz), according to MIL-STD810G	
Regulatory compliance	RoHS	
Electro-optical specifications		
Image format [pixels]	1280x1024	
Pixel pitch [µm]	12	
Integration type	Rolling shutter	
Active area and diagonal [mm]	15.36 x 12.29 (diagonal 19.67)	
Detector NETD (Noise Equivalent Temperature Difference) [mK]	<40 (at 30 Hz, 300K, F/1) available upon request	<50 (at 30Hz, 300K, F/1)
Spectral range [µm]	8-14	
Pixel operability	>99.5% (excluding 3 peripheral rows and columns)	
Max frame rate [Hz] [full frame]	60 (16bit DV, MIPI CSI-2); 40 (USB)	
Integration time range [µs]	20 - 65	
Analog-to-Digital [ADC] [bits]	14	
Command and control	via SAMTEC ST5 connector [16bit DV]; I2C [MIPI CSI-2]; GenCP over virtual COM port enumerated over the USB interface [USB]	
Digital output format	16bit DV, MIPI CSI-2, USB	
Trigger	via SAMTEC ST5 connector (16bit DV); NA (MIPI CSI-2, USB)	
Product selector guide		
Part number	XEN-000702	XEN-000701

advancedimaging@exosens.com



exosens.com

EXOSENS
REVEAL THE INVISIBLE